




MISSION-CRITICAL UNDERWATER INTERCONNECT SOLUTIONS

Most aggressive lead times in the industry · Vertically integrated and made in the USA
Custom solutions, no minimum order quantities


Accessible and responsive engineering support · Obsessed with quality and qualification
Superior technical designs for extended durability and performance



Seaking™ Fiber Optic

10K PSI open-face connectors,
cables and jumpers, plus
ruggedized transceivers and
media converters

- Ideal for data-intensive subsea applications:
towed-array sonar, well logging and monitoring, and ILI sensors
- Overmolded and PBOF butt-joint assemblies
- Full hydrostatic qualification test report available
- Wide range of fiber and hybrid fiber/electric layouts
- Singlemode and multimode
- <1.0db data loss for singlemode




DEEP WATER

SeaKing™ Fiber Optic


10K PSI open-face pressure-rated fiber optic connectors, cables, transceivers, and media converters




ENVIRONMENTAL OVERMOLDED FIBER OPTIC JUMPERS



PRESSURE-BALANCED OIL-FILLED (PBOF) HIGH-PRESSURE FIBER OPTIC ASSEMBLIES



SEAKING™ BCR OR FCR TO COMMERCIAL FIBER OPTIC PIGTAIL ASSEMBLY FOR I/O-TO-BOARD MODULE APPLICATIONS



KEY AND KEYWAY POSITIONS

Alternate Keyway Positions		
Key Position	Key Rotation	
	A°	B°
Normal (N)	150°	210°
A	75°	210°
B	95°	230°
C	140°	275°

